

Совки, шпатели, воронки, держатели

Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +7(727) 34-54-704

Беларусь +(375) 257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: aqs@nt-rt.ru || сайт: <https://abdos.nt-rt.ru/>

Dual Purpose Scoop, HDPE

- ABDOS Dual purpose Scoop is designed to combine the function of a scoop, weigh boat, and funnel to make this product economically beneficial.
- These Scoops are made from high quality anti-static polystyrene that is waterproof and reduces the probability of materials sticking to the scoop.
- These scoops have locking tabs that help to retain materials.
- These scoops can withstand powders, gels, and semi-solids.
- The broad tip design keeps the scoop stable while on the scale and enables materials to be easily scooped and dispensed.
- The dosage requirements for electron beam sterilization that results in sterilized products is determined by procedures that are compliant with ISO 11137.



STERILE E

Code	Size	Dimension	Colour	No./case
P11907	Large	127 x 90 mm	White	100
P11908	Small	127 x 63 mm	White	100



Scoop, HDPE

- These scoops are used for withdrawal and movement of solid, granulates, gels and other samples.
- Round bottom for better use.
- With precise formed filling edge and comfortable, stable and robust handle.
- Natural in colour.
- Superior chemical resistance.



Code	Capacity	Total Length	No./case
P11901	90 ml	180 mm	12
P11902	250 ml	240 mm	12
P11903	600 ml	300 mm	6
P11904	1100 ml	360 mm	6
P11905	1500 ml	400 mm	3



Weighing Boats, PS

- Abdos weighing boats are flexible with smooth surfaces to provide accurate pour-outs with minimal sample loss.
- Biologically inert and resistant to dilute weak acids, aqueous solutions, alcohols, and bases.
- All Abdos weighing boats are anti-static and facilitate the weighing of the static-affected sample.
- These boats can withstand temperature between 10°C to 70°C.
- Can be used with microwave moisture analysers.
- Suitable for use with food.
- Standard Weighing Boats are shallow with a wide, flat bottom to resist tipping.
- They have rounded corners to simplify transfer.
- Pour spout weighing boat have an innovative unique design for easy dispense of the sample without flexing the dish. 12-mil thickness provides good strength, stability and handling.



Weighing Boats Standard, PS				
Code	Size	Colour	L x W x H	No./case
P70501	Small	Blue	46 x 46 x 8 mm	250
P70502	Medium	Blue	85 x 85 x 24 mm	250
P70505	Large	Blue	140 x 140 x 22 mm	250

Weighing Boat with Pour Spout, PS				
Code	Size	Colour	L x W x H	No./case
P70503	Small	White	43 x 58 x 13 mm	250
P70504	Medium	White	83 x 132 x 26 mm	250
P70506	Large	White	108 x 183 x 26 mm	250



Spatula, PP

- Abdos Spatula is moulded in polypropylene.
- Spatula consists of a spoon on one side while the other end is a flat construction with a knife edge.
- The edge is helpful in breaking up crystals of different salts while the spoon is used to draw salts from containers.
- Suitable for use with food.



Spatula		
Code	Length	No./case
P70707	150 mm	120
P70708	200 mm	120



Funnel, PP

- Designed specifically for analytical chemistry.
- Each size takes a standard size filter paper.
- The body of the funnel is 60° angle.
- Provided with external and internal ribs.



Funnel, PP				
Code	Size Diameter	Internal Diameter	Stem Length	No./case
P70314	50 mm	50 mm	50 mm	36
P70315	62 mm	62 mm	67 mm	36
P70316	75 mm	75 mm	77 mm	36
P70317	100 mm	100 mm	95 mm	12



Funnel Holder, PP

- These are corrosion free and can hold funnels with diameter 3 in to 6 in.
- Extra plate provided can be placed to hold funnels with diameter 1 in to 3 in.
- Two tapered wedges are provided to have a firm grip on rods.



Code	Places	No./case
P70311	Single	6
P70312	Double	6



Powder Funnel, PP

- These Powder Funnels are used for transferring material in narrow bottles without spillage.
- Various sizes for different container sizes and volumes.
- Moulded from high quality virgin Polypropylene to ensure excellent results.



Code	Internal Diameter	No./case
P70318	65 mm	36



Separatory Funnel, PP

- ABDOS Separatory funnel is moulded from high quality virgin Polypropylene to ensure excellent clarity and strength.
- This Funnel is pear shaped and has screw cap for superior sealing and leak proof.
- This funnel comes with PTFE plug for easy usage.
- Push Fit Plugs make the assembly easy and convenient.



Code	Capacity	No./case
P70321	125 ml	2
P70322	250 ml	2
P70323	500 ml	2



Separatory Funnel Holder, PP

- These are corrosion free with a front opening that allows a clear view of the solution and allows unobstructed placement of separating funnels.
- Two tapered wedges are provided to have a firm grip on rods.



Code	Places	No./case
P70313	Single	6



Retort Stand, PP/PE Coated Rod

- Retort stand is used to attach clamp that holds test tubes and other equipment like burettes.
- It is used for titration, distillation and filtering of samples.
- It is available in both central and side holes.
- Base of the stand is PP and the rod is coated in PE.

Code	L x B, mm	Height of Rod	No./case
P70211	225 x 150 side hole	750 mm	1
P70212	300 x 200 centre hole	750 mm	1
P70213	301 x 200 side hole	750 mm	1



Burette Clamp, PP

- Burette clamps are used to hold burettes, test tubes, etc.
- Completely corrosion proof as it is moulded in polypropylene.
- Spring-loaded jack in the middle provides grip to the burette and prevents it from slipping.
- Two tapered wedges are provided to ensure firm grip on the rods.
- Available in both single and double clamp.

Code	Places	No./case
P70601	Single	6
P70602	Double	6



Water Bottle for Animal Species, PP/SS

- These narrow mouth bottles come with attached stainless steel pipe for release of liquid.
- Easy to fill, empty and wash.
- Leak proof.



Code	Capacity	Mouth Diamter	Height	No./case
P20511	125 ml	290 x 220 x 140 mm	97.6 mm	12
P20512	250 ml	430 x 270 x 150 mm	130.7 mm	12



Utility Tray, PP

- Moulded from high quality virgin Polypropylene to ensure excellent results.
- These Utility Trays are used for routine washing and keeping labware and transporting material.
- This tray is designed for easy grip and handling heavy loads.



Code	L x W x H	No./case
P90115	350 x 275 x 75 mm	10
P90116	360 x 310 x 130 mm	6



Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижегород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +7(727) 34-54-704

Беларусь +(375) 257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

По вопросам продаж и поддержки обращайтесь:

эл.почта: aqs@nt-rt.ru || сайт: <https://abdos.nt-rt.ru/>